



Main

Product or component type	Auxiliary contact
Device short name	PF
Range compatibility	Masterpact MasterPact NT Masterpact MasterPact NW
Signal contacts composition	1 NO/NC

Complementary

Auxiliary contacts type	Low level
Mounting mode	Fixed
Breaking capacity (A)	DC-12: 0.15 A at 250 V DC DC-12: 3 A at 24/48 V DC AC-12: 3 A at 24/48 V AC 50/60 Hz AC-12: 3 A at 240 V AC 50/60 Hz DC-12: 0.3 A at 125 V DC AC-12: 3 A at 380 V AC 50/60 Hz

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	11.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	40.0 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------