



Main

Range	MasterPacT
Range of product	MasterPact NT MasterPact NW MasterPact NW DC
Device short name	XF
Product or component type	Voltage release
Device application	Control
Voltage release type	Closing coil Instantaneous voltage release
Control type	Standard
[Uc] control circuit voltage	200...250 V AC 50/60 Hz 200...250 V DC
Circuit breaker mounting mode	Fixed
Range compatibility	Masterpact MasterPact NT Masterpact MasterPact NW Masterpact MasterPact NW DC

Complementary

Operating threshold	0.85...1.1 Un closing
Response time	55 ms +/- 10 % for MasterPact NT 70 ms +/- 10 % for MasterPact NW 800 A 70 ms +/- 10 % for MasterPact NW 1000 A 70 ms +/- 10 % for MasterPact NW 1250 A 70 ms +/- 10 % for MasterPact NW 1600 A 70 ms +/- 10 % for MasterPact NW 2000 A 70 ms +/- 10 % for MasterPact NW 2500 A 70 ms +/- 10 % for MasterPact NW 3200 A 70 ms +/- 10 % for MasterPact NW 4000 A 80 ms +/- 10 % for MasterPact NW 5000 A 80 ms +/- 10 % for MasterPact NW 6300 A
Supply holding power	4.5 VA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	1.162 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------