



Main

| | |
|-------------------------------|---|
| Range | MasterPacT |
| Range of product | MasterPact NT MasterPact NW MasterPact NW DC |
| Device short name | MX |
| Product or component type | Voltage release |
| Device application | Control |
| Voltage release type | Opening coil Instantaneous voltage release |
| Control type | Standard |
| [Uc] control circuit voltage | 200...250 V AC 50/60 Hz 200...250 V DC |
| Circuit breaker mounting mode | Fixed |
| Range compatibility | Masterpact MasterPact NT Masterpact MasterPact NW Masterpact MasterPact NW DC |

Complementary

| | |
|----------------------|--|
| Operating threshold | 0.7... 1.1 x Un opening |
| Response time | 50 ms +/- 10 % for MasterPact NT 50 ms +/- 10 % for MasterPact NW |
| Supply holding power | 4.5 VA |

Packing Units

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.000 cm |
| Package 1 Width | 6.000 cm |
| Package 1 Length | 8.500 cm |
| Package 1 Weight | 173.000 g |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 20 |
| Package 2 Height | 15.000 cm |
| Package 2 Width | 30.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 3.720 kg |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 320 |
| Package 3 Height | 45.000 cm |
| Package 3 Width | 80.000 cm |
| Package 3 Length | 120.000 cm |
| Package 3 Weight | 71.520 kg |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|