



### Main

Range	MasterPacT
Range of product	MasterPact NT
Device short name	XF com
Product or component type	Voltage release
Device application	Control
Voltage release type	Closing coil Instantaneous voltage release
Control type	Communicating
[Uc] control circuit voltage	24 V AC 50/60 Hz 24...30 V DC
Circuit breaker mounting mode	Drawout
Range compatibility	Masterpact MasterPact NT

### Complementary

Operating threshold	0.85...1.1 Un closing
Response time	55 ms +/- 10 %
Supply holding power	4.5 VA

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	6.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	1.167 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.