



### Main

Product or component type	Auxiliary contact
Device short name	SDE
Range compatibility	Masterpact MasterPact NT
Signal contacts composition	1 NO/NC

### Complementary

Auxiliary contacts type	Standard
Mounting mode	Drawout
[I <sub>th</sub> ] conventional free air thermal current	5 A
Breaking capacity (A)	DC-12: 0.15 A at 250 V DC DC-12: 3 A at 24/48 V DC DC-12: 0.3 A at 125 V DC
Minimum load	100 mA at 24 V

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	18.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	43.0 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	18 months
----------	-----------