



### Main

Range	MasterPacT
Range of product	MasterPact NT
Device short name	XF
Product or component type	Voltage release
Device application	Control
Voltage release type	Closing coil Instantaneous voltage release
Control type	Standard
[Uc] control circuit voltage	277 V AC 50/60 Hz
Circuit breaker mounting mode	Drawout
Range compatibility	Masterpact MasterPact NT

### Complementary

Operating threshold	0.85...1.1 Un closing
Response time	55 ms +/- 10 %
Supply holding power	4.5 VA

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	9.0 cm
Package 1 Length	6.0 cm
Package 1 Weight	1.169 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	18 months
----------	-----------