



Main

Range	MasterPacT
Range of product	MasterPact NT
Device short name	second MX
Product or component type	Voltage release
Device application	Control
Voltage release type	Second opening coil Instantaneous voltage release
Control type	Standard
[Uc] control circuit voltage	100...130 V AC 50/60 Hz 100...130 V DC
Circuit breaker mounting mode	Drawout
Range compatibility	Masterpact MasterPact NT

Complementary

Operating threshold	0.7...1.1 x Un opening
Response time	50 ms +/- 10 %
Supply holding power	4.5 VA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.3 cm
Package 1 Length	8.1 cm
Package 1 Weight	1.167 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.