



Main

| | |
|-------------------------------|--|
| Range | MasterPacT |
| Range of product | MasterPact NT |
| Device short name | second MX |
| Product or component type | Voltage release |
| Device application | Control |
| Voltage release type | Second opening coil Instantaneous voltage release |
| Control type | Standard |
| [Uc] control circuit voltage | 277 V AC 50/60 Hz |
| Circuit breaker mounting mode | Drawout |
| Range compatibility | Masterpact MasterPact NT |

Complementary

| | |
|----------------------|------------------------|
| Operating threshold | 0.7...1.1 x Un opening |
| Response time | 50 ms +/- 10 % |
| Supply holding power | 4.5 VA |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.0 cm |
| Package 1 Width | 9.0 cm |
| Package 1 Length | 6.0 cm |
| Package 1 Weight | 1.169 kg |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| Sustainable packaging | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|