

Main

Device short name	gear motor MCH
Product or component type	Gear motor mechanism MCH
Device application	Automatic spring charging
Range compatibility	MasterPact NT circuit breaker
Control type	Motor mechanism
[Uc] control circuit voltage	100...130 V AC 50/60 Hz
Circuit breaker mounting mode	Drawout

Complementary

Maximum charging time	3 s
Maximum power consumption in VA	180 VA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	12.0 cm
Package 1 Length	18.0 cm
Package 1 Weight	829.0 g

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
SCIP Number	8105062d-c949-4aef-a371-66dcfc82357e
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free plastic parts product
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	6

Contractual warranty

Warranty	18 months
----------	-----------