



Main

Range of product	MasterPact NT UL 489 MasterPact NT
Device short name	Modbus COM
Product or component type	Communication module
Range compatibility	Masterpact MasterPact NT Masterpact MasterPact NT UL 489

Complementary

Communication network type	Modbus
Mounting mode	Drawout
Localisation on device	Basic frame
[Us] rated supply voltage	24 V DC
Maximum supply current	0.03 A
Height	90 mm
Width	54 mm
Depth	58 mm

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	7.6 cm
Package 1 Length	9.3 cm
Package 1 Weight	1.09 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months
----------	-----------
