

### Main

Device short name	gear motor MCH
Product or component type	Gear motor mechanism MCH
Device application	Automatic spring charging
Range compatibility	MasterPact NW circuit breaker
Control type	Motor mechanism
[Uc] control circuit voltage	200...250 V DC
Circuit breaker mounting mode	Fixed

### Complementary

Maximum charging time	4 s
Maximum power consumption in VA	180 VA

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	13.1 cm
Package 1 Length	22.9 cm
Package 1 Weight	1.868 kg

### Offer Sustainability

SCIP Number	8105062d-c949-4aef-a371-66dcfc82357e
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Halogen content performance	Halogen free plastic parts product
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	14

### Contractual warranty

Warranty	18 months
----------	-----------