



Main

Range of product	Masterpact UR MasterPact NW MasterPact NW UL 489
Range	MasterPact
Device short name	M2c
Product or component type	Programmable contact
Device application	Control
Range compatibility	Masterpact MasterPact NW circuit breaker Masterpact MasterPact NW UL 489 circuit breaker Masterpact Masterpact UR circuit breaker




Complementary

Mounting mode	Drawout
[I _e] rated operational current	1.5 A at 48 V DC 1.8 A at 24 V DC 3 A at 380 V AC 5 A at 240 V AC 0.15 A at 250 V DC 0.4 A at 125 V DC
Minimum load	100 mA at 24 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.0 cm
Package 1 Length	8.2 cm
Package 1 Weight	70.0 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------