



Main

Range of product	Masterpact UR MasterPact NW MasterPact NW UL 489
Range	MasterPact
Device short name	M6c
Product or component type	Programmable contact
Device application	Control
Range compatibility	Masterpact MasterPact NW circuit breaker Masterpact MasterPact NW UL 489 circuit breaker Masterpact Masterpact UR circuit breaker

Complementary

Mounting mode	Drawout
[Ie] rated operational current	1.5 A at 48 V DC 1.8 A at 24 V DC 3 A at 380 V AC 5 A at 240 V AC 0.15 A at 250 V DC 0.4 A at 125 V DC
Minimum load	100 mA at 24 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	10.0 cm
Package 1 Length	11.0 cm
Package 1 Weight	368.0 g

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.