



### Main

Range	MasterPacT
Range of product	MasterPact NW MasterPact NW DC
Device short name	XF com
Product or component type	Voltage release
Device application	Control
Voltage release type	Closing coil Instantaneous voltage release
Control type	Communicating
[Uc] control circuit voltage	12 V DC
Circuit breaker mounting mode	Drawout
Range compatibility	Masterpact (MasterPact NW) Masterpact (MasterPact NW DC)

### Complementary

Operating threshold	0.85...1.1 Un closing
Response time	70 ms +/- 10 % for MasterPact NW 800 A 70 ms +/- 10 % for MasterPact NW 1000 A 70 ms +/- 10 % for MasterPact NW 1250 A 70 ms +/- 10 % for MasterPact NW 1600 A 70 ms +/- 10 % for MasterPact NW 2000 A 70 ms +/- 10 % for MasterPact NW 2500 A 70 ms +/- 10 % for MasterPact NW 3200 A 70 ms +/- 10 % for MasterPact NW 4000 A 80 ms +/- 10 % for MasterPact NW 5000 A 80 ms +/- 10 % for MasterPact NW 6300 A
Supply holding power	4.5 W

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.0 cm
Package 1 Length	6.0 cm
Package 1 Weight	1.168 kg

### Offer Sustainability

RECh Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------