



### Main

Product or component type	Auxiliary contact
Device short name	PF
Range compatibility	Masterpact MasterPact NW
Signal contacts composition	1 NO/NC

### Complementary

Auxiliary contacts type	Standard
Mounting mode	Drawout
Breaking capacity (A)	AC-12: 5 A at 480 V AC 50/60 Hz AC-12: 3 A at 690 V AC 50/60 Hz AC-12: 5 A at 240/380 V AC 50/60 Hz DC-12: 0.15 A at 250 V DC DC-12: 3 A at 24/48 V DC DC-12: 0.3 A at 125 V DC
Minimum load	100 mA at 24 V

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	4.7 cm
Package 1 Length	15.0 cm
Package 1 Weight	42.0 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	18 months
----------	-----------