



### Main

Product or component type	Auxiliary contact
Device short name	PF
Range compatibility	Masterpact MasterPact NW
Signal contacts composition	1 NO/NC

### Complementary

Auxiliary contacts type	Low level
Mounting mode	Drawout
Breaking capacity (A)	DC-12: 0.15 A at 250 V DC DC-12: 3 A at 24/48 V DC AC-12: 3 A at 24/48 V AC 50/60 Hz AC-12: 3 A at 240 V AC 50/60 Hz DC-12: 0.3 A at 125 V DC AC-12: 3 A at 380 V AC 50/60 Hz
Minimum load	2 mA at 15 V

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	11.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	36.0 g

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	18 months
----------	-----------