



Main

Product or component type	Auxiliary contact
Device short name	SDE
Range compatibility	Masterpact MasterPact NW
Signal contacts composition	1 NO/NC

Complementary

Auxiliary contacts type	Standard
Mounting mode	Drawout
[I _{th}] conventional free air thermal current	5 A
Breaking capacity (A)	AC-12: 5 A at 480 V AC 50/60 Hz AC-12: 3 A at 690 V AC 50/60 Hz AC-12: 5 A at 240/380 V AC 50/60 Hz DC-12: 0.15 A at 250 V DC DC-12: 3 A at 24/48 V DC DC-12: 0.3 A at 125 V DC
Minimum load	100 mA at 24 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.0 cm
Package 1 Length	7.3 cm
Package 1 Weight	70.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------