



Main

Product or component type	Auxiliary contact
Device short name	SDE
Range compatibility	Masterpact MasterPact NW
Signal contacts composition	1 NO/NC

Complementary

Auxiliary contacts type	Low level
Mounting mode	Drawout
Breaking capacity (A)	DC-12: 0.15 A at 250 V DC DC-12: 3 A at 24/48 V DC AC-12: 3 A at 24/48 V AC 50/60 Hz AC-12: 3 A at 240 V AC 50/60 Hz DC-12: 0.3 A at 125 V DC AC-12: 3 A at 380 V AC 50/60 Hz
Minimum load	2 mA at 15 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	11.0 cm
Package 1 Length	11.0 cm
Package 1 Weight	68.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------