



### Main

Device short name	EF contact
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact MasterPact NW
Signal contacts composition	1 NO/NC

### Complementary

Auxiliary contacts type	Standard
Auxiliary contacts operation	Connected position
Mounting mode	Drawout
[Ie] rated operational current	AC-12: 6 A at 690 V AC 50/60 Hz DC-12: 0.3 A at 250 V DC DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC AC-12: 6 A at 240/380 V AC 50/60 Hz AC-12: 6 A at 480 V AC 50/60 Hz
Minimum load	100 mA at 24 V

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	4.7 cm
Package 1 Length	14.5 cm
Package 1 Weight	36.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	22.0 cm
Package 2 Width	6.0 cm
Package 2 Length	23.0 cm
Package 2 Weight	360.0 g
Unit Type of Package 3	S03
Number of Units in Package 3	100
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	3.9 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------