



Main

Range	MasterPacT
Range of product	MasterPact NW MasterPact NW DC MasterPact NW NAVY
Device short name	MN
Product or component type	Voltage release
Device application	Control
Voltage release type	Opening coil Undervoltage release
Control type	Standard
[Uc] control circuit voltage	200...250 V AC 50/60 Hz 200...250 V DC
Circuit breaker mounting mode	Drawout
Range compatibility	Masterpact MasterPact NW Masterpact MasterPact NW DC

Complementary

Operating threshold	0.35...0.7 x Un opening 0.85 Un closing
Response time	90 ms +/- 5 %
Supply holding power	4.5 VA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.0 cm
Package 1 Length	8.2 cm
Package 1 Weight	178.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------