



Main

Device short name	gear motor MCH
Product or component type	Gear motor mechanism MCH
Device application	Automatic spring charging
Range compatibility	Masterpact MasterPact NW circuit breaker
Control type	Motor mechanism
[Uc] control circuit voltage	48 V AC 50/60 Hz 48...60 V DC
Circuit breaker mounting mode	Drawout

Complementary

Maximum charging time	4 s
Maximum power consumption in VA	180 VA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.6 cm
Package 1 Width	13.0 cm
Package 1 Length	22.9 cm
Package 1 Weight	1.864 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.