



Main

Range	Vigilohm
Device short name	ZX
Product or component type	Limiting impedance
Range compatibility	Vigilohm

Complementary

Network rated voltage	0...500 V - AC at 2.5 Hz (1 MOhm) 0...500 V - AC at 50 Hz (1500 Ohm)
Net weight	3.5 kg
Width	380 mm
Height	190 mm
Depth	200 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	22.000 cm
Package 1 Width	21.000 cm
Package 1 Length	40.000 cm
Package 1 Weight	5.684 kg
Unit Type of Package 2	S06
Number of Units in Package 2	4
Package 2 Height	73.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	34.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------