



Main

Range	Vigilohm
Range of product	Vigilohm
Device short name	HRP
Product or component type	Hospital remote panel
Range compatibility	Vigilohm Vigilohm IM IM20-H
Sound signalling	Insulation or electrical fault: buzzer adjustable 80 dB

Complementary

Auxiliary supply voltage	24 V DC
Current consumption	65 mA
Material	Plastic
Control type	Push-button: test installation insulation Push-button: stop alarm buzzer
Local signalling	Insulation fault: indicator light (orange) Electrical fault: indicator light (red) Normal operation: indicator light (green)
Net weight	0.5 kg
Width	170 mm
Height	170 mm
Depth	20 mm

Environment


IP degree of protection	IP54
IK degree of protection	IK08
Operating altitude	2000 m
Relative humidity	90 %
Standards	IEC 60364-7-710: medical location IEC 61557-8: safety IEC 60601-1: medical electrical equipment
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-25...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	20.6 cm
Package 1 Length	21.5 cm
Package 1 Weight	342.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm

Package 2 Length	60.0 cm
Package 2 Weight	4.13 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------