



Main

Range	Affle Plus
Product or component type	Switched socket
Device application	Switch & socket
Device presentation	Mechanism
Outlet poles configuration	3P with shutter
Outlet standard description	With earthing contact
Outlet standard	BS 1363
Type of packing	Flow-pack
Sale per indivisible quantity	1
Number of terminals	3

Complementary

Socket number	1
Device mounting	Flush
Fixing mode	Screw
Surface finish	Glossy
Surface treatment	Untreated mechanism cover
Rated current	15 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Service life in cycles	15000 cycles
Electrical durability	5000 cycles
Connections - terminals	Pillar terminal
Screwdriver shape	Philips No 2
Number of cables	2
Clamping connection capacity	2.5...4 mm ² for rigid cable(s) 2.5...4 mm ² for stranded cable(s) 2.5...4 mm ² for flexible cable(s)
Wire stripping length	14 mm
Material	PC (polycarbonate) Brass
Height	86 mm
Width	86 mm
Depth	33.6 mm
Embedding depth	23.7 mm
Net weight	0.07 kg

Environment

Ambient air temperature for storage	-5...60 °C
Ambient air temperature for operation	-5...45 °C
Relative humidity	0...95 %
Standards	BS 546 MS 1577
Product certifications	SIRIM
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	78.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	786.0 g
Unit Type of Package 3	CAR
Number of Units in Package 3	120
Package 3 Height	21.0 cm
Package 3 Width	39.9 cm
Package 3 Length	46.9 cm
Package 3 Weight	9.932 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations