



Main

Range	Affle Plus
Product or component type	Switch
Device application	Control switch
Colour tint	White

Complementary

Device mounting	Flush
Material	Polycarbonate: surround
Width	86 mm
Height	86 mm
Depth	7.7 mm

Environment

Maximum ambient air temperature for operation	35 °C
Relative humidity	0...95 %
Standards	BS 5733 IEC 60670-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	12.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	381.0 g
Unit Type of Package 3	PAL
Number of Units in Package 3	5760
Package 3 Height	100.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	81152.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations