



### Main

Range	Affle Plus
Product or component type	Socket-outlet
Device application	Switch & socket
Outlet poles configuration	2P
Load type	Resistive
Colour tint	White
Main colour tint	White

### Complementary

Device presentation	Mechanism
Device mounting	Flush
Number of gangs	1 gang
Material	Polycarbonate surround
Fixing mode	By screws
Width	86 mm
Height	86 mm
Depth	8 mm

### Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	5000 m
IP degree of protection	IP20
Standards	IEC 60670-1 BS 5733

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	13.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	396.0 g
Unit Type of Package 3	PAL
Number of Units in Package 3	5760

Package 3 Height	100.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	84032.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations