

Main

Range	Affle Plus
Product or component type	Socket-outlet
Device application	Switch & socket
Outlet poles configuration	2P
Load type	Resistive
Colour tint	White
Main colour tint	White

Complementary

Device presentation	Mechanism
Device mounting	Flush
Number of gangs	1 gang
Material	Polycarbonate surround
Fixing mode	By screws
Width	86 mm
Height	86 mm
Depth	8 mm

Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	5000 m
IP degree of protection	IP20
Standards	IEC 60670-1 BS 5733

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	13.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	396.0 g
Unit Type of Package 3	PAL
Number of Units in Package 3	5760

Package 3 Height	100.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	84032.0 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No