



Main

Range	Affle Plus
Product or component type	Switched fuse mechanism
Device presentation	Complete mechanism
Cover frame colour tint	White

Complementary

Pilot light	Neon indicator
Switch function	2-pole switch
Number of gangs	1 gang
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: cover Polycarbonate: dolly PA66 GF30: tip
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	13 A at 250 V AC, resistive
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Screw terminal Pillar terminal
Terminal identifier	N in L out N out L in Earth
Tightening torque	0.4 N.m
Width	86 mm
Height	86 mm
Depth	32.4 mm
Net weight	0.093 kg

Environment

Standards	BS 1363-4
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	102.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	1025.0 g
Unit Type of Package 3	CAR
Number of Units in Package 3	120
Package 3 Height	21.0 cm
Package 3 Width	39.9 cm
Package 3 Length	46.9 cm
Package 3 Weight	12.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations