



Main

Range	Affle Plus
Product or component type	Data socket
Colour tint	White

Complementary

Device mounting	Flush
Communication network category	Data: 5e
Rated current	1.5 A
Number of gangs	2 gangs
Material	Polycarbonate: plastic part
Contacts material	Housing: PC Contact: phosphor bronze with gold plating
Contact resistance	1 μ Ohm
Insulation resistance	\geq 200 mOhm
AWG gauge	AWG 26...AWG 22 (4 twisted pair cables)
Minimum return loss	23 dB
Width	86 mm
Height	86 mm
Depth	33.5 mm

Environment

Dielectric strength	1000 V for 60 s at 60 Hz
Environmental characteristic	UV resistant
Maximum ambient air temperature for operation	35 °C
Relative humidity	0...95 %
Standards	IEC 60670-1 BS 5733

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	55 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm

Package 2 Length	19 cm
Package 2 Weight	446 g
Unit Type of Package 3	PAL
Number of Units in Package 3	1536
Package 3 Height	100 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	93632 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations