



Main

Range	Affle Plus
Product or component type	TV/FM/SAT socket
TV socket type	TV
Type of signal	TV-FM
Colour tint	White

Complementary

Wiring device mounting	Flush
Method of access	Master
Average impedance	75 Ohm
Number of gangs	2 gangs
Material	Polycarbonate: surround Polycarbonate: grid plate
Width	86 mm
Height	86 mm
Depth	24 mm

Environment

Ambient air temperature for operation	-5...45 °C
Relative humidity	0...95 %
Standards	BS 5733 IEC 60670-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	68 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	689 g
Unit Type of Package 3	CAR
Number of Units in Package 3	120
Package 3 Height	21 cm
Package 3 Width	39.9 cm
Package 3 Length	46.9 cm
Package 3 Weight	8.768 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes