



Main

Range	Affle Plus
Product or component type	Switch
Device application	Control switch
Load type	Incandescent lamp Inductive Resistive Fluorescent lamp
Colour tint	White

Complementary

Device mounting	Flush
Switch function	1-way
Cable cross section	4 Mm ² stranded cable 2.5 Mm ² solid cable 2.5 Mm ² stranded cable 6 x 4 mm ² solid cable for AC
Rated current	10 AX at 250 V AC
Number of gangs	3 gangs
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: surround Polycarbonate: actuator
Connections - terminals	Brass terminal Screw terminal
Embedding depth	24.9 mm
Width	86 mm
Height	86 mm
Depth	35.6 mm

Environment

Maximum ambient air temperature for operation	35 °C
Relative humidity	0...95 %
Operating altitude	5000 m
Product certifications	IEC
Standards	MS IEC 60669-1 IEC 60669-1 BS EN 60669-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	94 g
Unit Type of Package 2	BB1

Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	757 g
Unit Type of Package 3	CAR
Number of Units in Package 3	96
Package 3 Height	21 cm
Package 3 Width	39.9 cm
Package 3 Length	46.9 cm
Package 3 Weight	9.584 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations