



### Main

Range	Affle Plus
Product or component type	Switched socket
Device application	Switch & socket
Device presentation	Mechanism
Outlet poles configuration	3P with shutter
Outlet standard description	With earthing contact
Outlet standard	BS 1363
Type of packing	Flow-pack
Sale per indivisible quantity	1
Number of terminals	3

### Complementary

Socket number	2
Device mounting	Flush
Fixing mode	Screw
Surface finish	Glossy
Surface treatment	Untreated mechanism cover
Rated current	13 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Service life in cycles	15000 cycles
Electrical durability	15000 cycles
Connections - terminals	Pillar terminal
Screwdriver shape	Philips No 2
Number of cables	2
Clamping connection capacity	2.5...4 mm <sup>2</sup> for rigid cable(s) 2.5...4 mm <sup>2</sup> for stranded cable(s) 2.5...4 mm <sup>2</sup> for flexible cable(s)
Wire stripping length	14 mm
Material	PC (polycarbonate) Brass
Height	86 mm
Width	146 mm
Depth	29.2 mm
Embedding depth	18.3 mm
Net weight	0.114 kg

### Environment

Ambient air temperature for storage	-5...60 °C
Ambient air temperature for operation	-5...45 °C
Relative humidity	0...95 %
Standards	BS 1363 MS 589
Product certifications	SIRIM
IP degree of protection	IP20

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	8.6 cm
Package 1 Length	14.6 cm
Package 1 Weight	121 g
Unit Type of Package 2	BB1
Number of Units in Package 2	7
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	850 g
Unit Type of Package 3	CAR
Number of Units in Package 3	84
Package 3 Height	21 cm
Package 3 Width	39.9 cm
Package 3 Length	46.9 cm
Package 3 Weight	10.7 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations