

Main

Range of product	Acti9
Device short name	iOF
Product or component type	OC contact
Signal contacts composition	1 C/O

Complementary

[Ie] rated operational current	3 A at 415 V AC 6 A at 250 V AC
Mounting mode	Fixed
Mounting support	35 mm DIN rail
9 mm pitches	2
Height	77 mm
Width	18 mm
Depth	75 mm
Colour	White
Range compatibility	Acti 9 Acti9 iSW
Auxiliary connection terminal	Screw terminal 10 mm ²

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.500 cm
Package 1 Width	7.500 cm
Package 1 Length	8.300 cm
Package 1 Weight	62.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	9
Package 2 Height	8.500 cm
Package 2 Width	9.300 cm
Package 2 Length	22.400 cm
Package 2 Weight	626.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	7.959 kg

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	No
SCIP Number	6ab3defc-4d52-4456-bd38-c6ef27b8549e
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1

Contractual warranty

Warranty	18 months
----------	-----------