



Main

| | |
|---------------------------|-----------|
| Range of product | Acti9 |
| Product name | Acti9 iSO |
| Product or component type | Bell |
| Device short name | iSO |

Complementary

| | |
|-------------------------------|---|
| [Us] rated supply voltage | 230 V AC at 50/60 Hz |
| Power consumption in VA | 5 VA |
| Mounting mode | Clip-on |
| Mounting support | 35 mm symmetrical DIN rail |
| 9 mm pitches | 2 |
| Height | 81 mm |
| Width | 18 mm |
| Depth | 72 mm |
| Net weight | 77 g |
| Auxiliary connection terminal | Tunnel type terminalsrigid 4 mm ² Tunnel type terminalsflexible 4 mm ² Tunnel type terminalsflexible with ferrule 4 mm ² |
| Wire stripping length | 12 mm for bottom connection |
| Tightening torque | 1.3 N.m bottom |

Environment

| | |
|---------------------------------------|--|
| Noise level | 80 dB |
| Type of sound | Bell |
| IP degree of protection | IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529 |
| Ambient air temperature for operation | -10...40 °C |
| Ambient air temperature for storage | -25...60 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.8 cm |
| Package 1 Width | 6.6 cm |
| Package 1 Length | 8.5 cm |
| Package 1 Weight | 59 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 12 |
| Package 2 Height | 8.5 cm |
| Package 2 Width | 10 cm |
| Package 2 Length | 22.7 cm |

| | |
|------------------------------|----------|
| Package 2 Weight | 767 g |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 144 |
| Package 3 Height | 30 cm |
| Package 3 Width | 30 cm |
| Package 3 Length | 40 cm |
| Package 3 Weight | 9.712 kg |

Offer Sustainability

| | |
|-----------------------------|---|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Halogen content performance | Halogen free product |