



### Main

Range of product	IID ISW 40...125 ISW-NA IC60
Product or component type	Rotary handle
Accessory / separate part type	Control accessories
Handle colour	Black
Rotary handle mounting style	Extended

### Complementary

Mounting mode	Drawout Fixed
Rotary handle padlocking	Lockable in O position 3 padlocks max Padlock in OFF position
Rotary handle mounting location	Front Lateral

### Environment

IP degree of protection	IP55
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	12.3 cm
Package 1 Length	47.0 cm
Package 1 Weight	670.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.872 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	45.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	47.488 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------