



Main

Range of product	ISW-NA IC60 IID ISW 40...125
Product or component type	Rotary handle
Accessory / separate part type	Control accessories
Handle colour	Red
Rotary handle mounting style	Extended

Complementary

Mounting mode	Drawout Fixed
Rotary handle padlocking	Padlock in OFF position 3 padlocks max Lockable in O position
Rotary handle mounting location	Lateral Front

Environment

IP degree of protection	IP55
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.700 cm
Package 1 Width	12.500 cm
Package 1 Length	47.500 cm
Package 1 Weight	658.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	8.800 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------