



## Main

Range	Acti9
Product name	Acti9 STI
Product or component type	Fuse-disconnector
Device short name	STI
Poles description	2P

## Complementary

[In] rated current	2 A 4 A 6 A 10 A 16 A 20 A 25 A
Fuse curve	AM GG
Fuse size	10.3 x 38 mm
[Ue] rated operational voltage	500 V AC
[Ui] rated insulation voltage	500 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	81 mm
Width	36 mm
Depth	75 mm
Colour	White
Connections - terminals	Screw clamp terminals1 cable(s) 0.75...10 mm <sup>2</sup> rigid Screw clamp terminals1 cable(s) 0.5...6 mm <sup>2</sup> flexible Screw clamp terminals2 cable(s) 0.75...4 mm <sup>2</sup> rigid Screw clamp terminals2 cable(s) 0.5...6 mm <sup>2</sup> flexible
Wire stripping length	12 mm
Tightening torque	2 N.m


## Environment

Standards	IEC 60269-1/2 IEC EN 60947-3
IP degree of protection	IP20
Pollution degree	3
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	3.500 cm
Package 1 Length	8.500 cm
Package 1 Weight	109.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	2.750 cm
Package 2 Width	30.000 cm
Package 2 Length	20.000 cm
Package 2 Weight	705.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	8.944 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product