



### Main

Range	Acti9
Product name	Acti9 iSW
Product or component type	Switch disconnecter
Device short name	iSW
Device application	Control
Poles description	3P
Utilisation category	AC-22A
Suitability for isolation	Yes

### Complementary

[Ie] rated operational current	32 A at 415 V AC 50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60669-2-4
[Uimp] rated impulse withstand voltage	4 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	4
Height	77 mm
Width	36 mm
Depth	70 mm
Colour	White
Mechanical durability	300000 cycles
Electrical durability	30000 cycles
Connections - terminals	Tunnel type terminals - 10 mm <sup>2</sup> - rigid Tunnel type terminals - 10 mm <sup>2</sup> - flexible Tunnel type terminals - 10 mm <sup>2</sup> - flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1.2 N.m







### Environment

Standards	EN/IEC 60669-2-4
IP degree of protection	IP4
Pollution degree	2
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	117.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	8.5 cm
Package 2 Width	9.5 cm
Package 2 Length	22.0 cm
Package 2 Weight	751.41 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	9.452 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------