



Main

Range	Acti9
Product name	Acti9 iSW
Product or component type	Switch disconnecter
Device short name	iSW
Device application	Isolation Control
Poles description	4P
Utilisation category	AC-22A
Suitability for isolation	Yes

Complementary

[Ie] rated operational current	40 A at 415 V AC 50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
[Icm] rated short-circuit making capacity	5 kA switch-disconnector alone
[Icw] rated short-time withstand current	1260 A
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
9 mm pitches	8
Height	85 mm
Width	72 mm
Depth	73 mm
Colour	White
Mechanical durability	20000 cycles
Electrical durability	15000 cycles
Connections - terminals	Tunnel type terminals (top or bottom) - $\leq 1 \times 50 \text{ mm}^2$ - rigid Tunnel type terminals (top or bottom) - $\leq 1 \times 35 \text{ mm}^2$ - flexible Tunnel type terminals (top or bottom) - $\leq 1 \times 35 \text{ mm}^2$ - flexible with ferrule
Wire stripping length	14 mm
Tightening torque	3.5 N.m

Environment

Standards	IEC 60947-3 EN 60947-3
IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	7.000 cm
Package 1 Length	9.300 cm
Package 1 Weight	336.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	2.780 cm
Package 2 Width	30.000 cm
Package 2 Length	20.000 cm
Package 2 Weight	1.048 kg
Unit Type of Package 3	S03
Number of Units in Package 3	33
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	11.964 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------