



Main

Range of product	PowerLogic
Product or component type	Heavy duty capacitor
Network frequency	50/60 Hz
Series name	HDuty
Network harmonic content	$\leq 20 \%$
Electrical parameters	50 kvar 50 Hz
Maximum permissible voltage	1.1 x Un (8 hours over 24 hours)
Continuous overcurrent capacity	1.8 x In
Rated voltage	440 V AC 50/60 Hz

Complementary

Dielectric losses	$< 0.2 \text{ W/kvar}$
Power losses	$< 0.5 \text{ W/kVAr}$
Capacitance tolerance	- 5 % to 10 %
Voltage test	2.15 x Un AC between terminals for 10 s $\leq 660 \text{ V}$ - 3 kV AC between terminal and container for 10 s $\geq 660 \text{ V}$ - 6 kV AC between terminal and container for 10 s
Inrush current	250 x In
Maximum switching operation per year	7000
Service life in hours	130000 h
Dielectric material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)
Impregnation material	Non-PCB dry PUR resin Biodegradable
Type of installation	Indoor installation
Connections - terminals	Stud terminals
Mounting mode	Upright/horizontal
Diameter	136 mm
Height	321 mm
Net weight	5.3 kg






Environment

Standards	IEC 60831-1 IEC 60831-2
IP degree of protection	IP00
Operating altitude	2000 m
Temperature class	D
Ambient air temperature for operation	-25...55 °C
Relative humidity	95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	18.5 cm
Package 1 Length	38 cm
Package 1 Weight	5.334 kg
Unit Type of Package 2	S06
Number of Units in Package 2	12
Package 2 Height	74 cm
Package 2 Width	60 cm
Package 2 Length	80 cm
Package 2 Weight	64.008 kg
Unit Type of Package 3	S06
Number of Units in Package 3	12
Package 3 Height	74 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	64.008 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------