

### Main

Product brand	Schneider Electric
Range	Wiser
Product name	Wiser Micro module switch
Product or component type	Connected switch
Device presentation	Module

### Complementary

Device mounting	Flush
Technology type	Electronic
Mobile App name	Wiser by SE
Concentrator compatibility	Wiser hub generation 1
Surface finish	Matt
Load type	Incandescent lamp: 2200 W at 230 V AC Halogen lamp: 2000 W at 230 V AC Motor: 1000 VA at 230 V AC LV halogen lamps: 1050 VA at 12 V AC (electronic transformer) LV halogen lamps: 500 VA at 12 V AC (wound transformer) LED lamp: 100 W at 230 V AC Compact fluorescent lamp: 100 W at 230 V AC
[Ue] rated operational voltage	220...240 V
Network type	AC
Network frequency	50/60 Hz
Rated current	10 AX
Standby consumption	Max. 0.3 W
Associated fuse rating	16 A
Local signalling	Programming indication: 1 LED (green, orange and red)
Number of outputs	1
Control type	Remote control by auxiliary push-button Remote control Wiser App
Software name	Wiser App: enable timer mode Wiser App: management of the pulse generator Wiser App: upgrade device firmware
Maximum number of connected devices	Bluetooth: 15
Communication network type	Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m
System requirements	Android 5.1 or higher Wiser App Apple iOS 10.3 or higher Wiser App Bluetooth 4.1 or higher Bluetooth
Connected auxiliaries	Maximum 10 auxiliary push-buttons
Wiring configuration	With neutral
Connections - terminals	Screw terminals
Number of loop terminals	2
Clamping connection capacity	1.5...2.5 mm <sup>2</sup> for solid cable(s) 1.5...2.5 mm <sup>2</sup> for solid stranded cable(s)
Shape of screw head	Pozidriv No 1 and combi
Tightening torque	0.5 N.m

Mounting support	Installation box Wall box
Type of installation	Indoor installation
Embedding depth	22 mm
Depth	22 mm
Width	43 mm
Height	43 mm

## Environment

Operating altitude	<= 2000 m
Ambient air temperature for operation	0...35 °C
IP degree of protection	IP20
Environmental characteristic	Indoor use
Standards	EN 60669-2-5 IEC 60669-2-5 CE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	80.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.715 kg

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No