



Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting: : 100 W Incandescent lamps: : 2000 W - 230 V Halogen lamp: : 1000 W - 230 V Halogen lamp with standard electronic transformer: 1000 VA Halogen lamp with standard ferromagnetic transformer: 1000 VA Fluorescent tube: 900 VA, 100 µF
Colour tint	White

Complementary

Network frequency	50/60 Hz
Input function	Switch External trigger
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	10...1000 lux
Horizontal detection angle	360 °
Mounting height	2.5 m

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.2 cm
Package 1 Width	11.7 cm
Package 1 Length	17.7 cm
Package 1 Weight	462 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	40 cm
Package 2 Width	31 cm
Package 2 Length	50 cm
Package 2 Weight	10.29 kg
Unit Type of Package 3	P12
Number of Units in Package 3	160
Package 3 Height	95 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	88.92 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins