



Main

Range compatibility	Wiser hub
Range	Wiser
Concentrator compatibility	Wiser hub generation 1
Product or component type	Window/door contact
Mobile App name	Wiser by SE
Colour tint	White
Supply	Battery 3 V / CR2450

Complementary

Device application	Security
Battery life	5 year(s)
Communication network type	Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m
Device composition	Sensor 50 mm x 33 mm x 16.3 mm Magnet 50 mm x 9 mm x 9 mm
Alive signal	48/day
Magnet gap	< 18 mm on wood and plastic surface < 10 mm on metallic surface
Provided equipment	User manual Battery Adhesive tape Screws
Mounting mode	By screws Adhesive
Mounting support	Window frame Door frame
Net weight	30 g
Standards	IEC 60669-2-5 EN 60669-2-5
Product certifications	CE[RETURN]Zigbee 3.0[RETURN]CB[RETURN]RCM[RETURN]EAC
Market segment	Residential

Environment

IP degree of protection	IP20
Relative humidity	10...95 %
Ambient air temperature for operation	-10...50 °C
Operating altitude	<= 2000 m
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	84.0 g

Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.875 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information