

### Main

Accessory / separate part designation	Incandescent bulb
Accessory / separate part type	Incandescent bulb
Accessory / separate part category	Lighting accessories
[Us] rated supply voltage	220...260 V AC
Signalling type	Steady
Power dissipation in W	6 W
Signalling colour	Clear
Diameter	18 mm
Length	35 mm
Sale per indivisible quantity	1




### Complementary

Bulb base	BA 15d
-----------	--------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.800 cm
Package 1 Width	1.800 cm
Package 1 Length	3.700 cm
Package 1 Weight	5.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5.000 cm
Package 2 Width	6.500 cm
Package 2 Length	13.000 cm
Package 2 Weight	74.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	280
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.403 kg

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
RoHS exemption information	 Yes

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	62

### Contractual warranty

Warranty	18 months
----------	-----------