



Main

Range compatibility	Harmony XVM Optimum
Accessory / separate part categor	Lighting accessory
Accessory / separate part type	Super bright LED
Accessory / separate part destination	Beacon and indicator bank
Bulb base	BA 15d
Signalling type	Steady
Signalling colour	Green
[Us] rated supply voltage	24 V AC/DC
Luminance	900 cd/m ²
Sale per indivisible quantity	1

Complementary

Net weight	0.009 kg
------------	----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	6.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	14.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	48
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.116 kg
Unit Type of Package 3	P06
Number of Units in Package 3	1536
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	31 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------