



Main

Product or component type	Switched socket
Device application	Power supply
Device presentation	Complete product
Outlet poles configuration	2P + 3P with shutter
Colour tint	Dark grey
Type of packing	Flow-pack
Main colour tint	Dark grey

Complementary

Rated current	16 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Socket number	2
Outlet standard description	With earthing contact
Outlet standard	Universal
Number of gangs	1 gang
Service life in cycles	20000 cycles
Electrical durability	5000 cycles
Material	Polycarbonate: grid plate Polycarbonate: surround
Surface finish	Glossy
Surface treatment	Painted cover plate
Device mounting	Surface
Height	86 mm
Width	86 mm
Depth	27.5 mm

Environment

IP degree of protection	IP20
Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Standards	IEC 60884-2-3

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	103.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.03 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	6.18 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations