



## Main

Product or component type	USB charger + switched socket
Fixing mode	By screws

## Complementary

Outlet standard	British
Outlet standard description	With earthing contact
Integrated connection type	2 USB type A 5 V DC 2.1 A 1 socket-outlet 250 V AC 13 A 50/60 Hz
Device mounting	Surface
Device presentation	Complete product
Mounting support	Mounting box
Outlet poles configuration	3P with shutter
Colour tint	Dark grey
Surface finish	Matt
Surface treatment	Untreated
Type of packing	Flow-pack
Quantity per set	Set of 10
Ambient air temperature for storage	-5...60 °C
Protection type	Thermal protection Current protection
Dielectric strength	2000 V
Ambient air temperature for operation	0...40 °C
Service life in cycles	5000 cycles
Connections - terminals	Screw terminal
Number of terminals	3
Screwdriver shape	Phillips combined
Number of cables	2
Clamping connection capacity	1.5...4 mm <sup>2</sup> for rigid cable(s) 1.5...4 mm <sup>2</sup> for stranded cable(s) 1.5...4 mm <sup>2</sup> for flexible cable(s)
Material	PC (polycarbonate): grid plate PC (polycarbonate): surround
Wire stripping length	12 mm
Height	86 mm
Width	86 mm
Depth	38.2 mm
Embedding depth	29.3 mm
Standards	UL 1310 UL 498 UL 94

## Environment

IP degree of protection	IP20
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	109.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.09 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	6.54 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>