



Main

Product or component type	Switched socket
Device application	Power supply
Device presentation	Complete product
Outlet poles configuration	3P with shutter
Type of packing	Flow-pack

Complementary

Rated current	15 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Socket number	1
Outlet standard description	With earthing contact
Outlet standard	British BS 546
Number of gangs	1 gang
Pilot light	LED
Service life in cycles	20000 cycles
Electrical durability	5000 cycles
Connections - terminals	Screw terminal
Material	Polycarbonate: grid plate Polycarbonate: surround
Surface finish	Glossy
Surface treatment	Painted cover plate
Device mounting	Surface
Fixing mode	Screw
Height	86 mm
Width	86 mm
Depth	32.6 mm

Environment

IP degree of protection	IP20
Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Standards	BS 546 MS 1577 SS 472
Product certifications	SIRIM

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	91.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	955.0 g
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	6230.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations