



Main

Product or component type	Blank plate
Number of gangs	2 gangs
Colour tint	Dark grey

Complementary

Material	Polycarbonate: plastic part
Device mounting	Flush Surface
Width	147 mm
Height	87 mm
Depth	14.7 mm




Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	31.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	310.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
