



Main

Product or component type	Blank plate
Number of gangs	2 gangs
Colour tint	Wood

Complementary

Material	Polycarbonate: plastic part
Device mounting	Flush Surface
Width	147 mm
Height	87 mm
Depth	14.7 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	8.6 cm
Package 1 Length	14.7 cm
Package 1 Weight	31 g
Unit Type of Package 2	BB1
Number of Units in Package 2	60
Package 2 Height	210 cm
Package 2 Width	300 cm
Package 2 Length	395 cm
Package 2 Weight	2942 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations